


Spare parts list: Sagoma System










Dietronic S.R.L. – Lubricating Technology

Via Madre Teresa di Calcutta, 9/13
26866 Sant'Angelo Lodigiano (LO) - Italia
Tel +39 0371 210129
Fax +39 0371 214321
info@dietronic.eu
www.dietronic.eu












Machine's components


Machine's components

<i>Picture</i>	<i>Code</i>	<i>Description and code</i>	<i>Supplier</i>	<i>Recommended pieces</i>
	5000628	Nozzle with 0,4 mm hole	Dietronic	5
	5000602	PTFE O-Ring with 6 holes	Dietronic	10
	G000018	Complete modular Manifold	Dietronic	\
	5001700	High frequency valve	Dietronic	5
	8562305	Cartridge heating resistance	Rotfil	5
	5001120	Proportional valve - ITV3030	SMC	1
	5000610	Nitrile rubber gasket	Dietronic	\
	8561010	Pressure sensor - PU5404	IFM	1
	5000103	Solenoid valve - K8000-303-K23	Dietronic	\










Machine's components

<i>Picture</i>	<i>Code</i>	<i>Description and code</i>	<i>Supplier</i>	<i>Recommended pieces</i>
	8565000	MXP electrical board	Dietronic	1
	8565001	Flat cable 140mm	Dietronic	\
	8565002	Flat cable 40mm	Dietronic	\
	8565003	Temperature sensor	Dietronic	1
	8565005	EVP electronic board 24V	Dietronic	1
	8565006	RSEL electronic board	Dietronic	1
	8561500	Encoder 2000ppr - RHI 503 59	Leine Linde	\
	8561000	Pressure sensor - PA9024	IFM Electronic	\
	8561018	Capacitive sensor - KG600	IFM Electronic	\










Tank's components







Tank components

<i>Picture</i>	<i>Code</i>	<i>Description and code</i>	<i>Supplier</i>	<i>Recommended pieces</i>
	5011054	Digital pressure sensor - ISE40A-01-P-L	SMC	\
	5001400	Filter holder - BPE1XB06WN06XX	UFI Filters	\
	5001405	Oil filter 90 µm - ESE11NMF	UFI Filters	2
	5001594	Level switch – LMD1	Elettrotec	1
	5001403	Metal filter 125 µm - ESB11B04XMF	UFI Filters	2
	5001122	Modular filter regulator - AW40-F04-B	SMC	\
	5001123	Air switch - VHS40-F04A	SMC	\
	5001124	Mounting spacer - Y400T	SMC	\
	5001121	Proportional valve – ITV1030	SMC	\

Tank components

<i>Picture</i>	<i>Code</i>	<i>Description and code</i>	<i>Supplier</i>	<i>Recommended pieces</i>
	5011662	Wheel with break – 535403	Tellure	\
	5001906	Bayonet plate - GN 442-32-G3/4-1-BL	Elesa	\
	5001907	Tank's oil cap - PR.137-PF-C1	Elesa	\
	5001595	Column level indicator - HCX.254-M12	Elesa	1
	8562302	Threaded immersion heater - CRZ-GTP	Rotfil	\
	5001102	Solenoid valve 5/2 - SY5120-5YO-01F-Q	SMC	1
	8561001	Level probe - E43203	IFM	\
	8561002	Coaxial sensor - E43211	IFM	\
	8561003	Level tank sensor - LR7000	IFM	1

Tank components






Picture	Code	Description and code	Supplier	Recommended pieces
	5011662	Membrane oil pump	Dietronic	1
	5001522	Pneumatic valve - DG100H003	Omal	\
	5001907	Pressure regulator - SFN.70-BA+F	SMC	1
	8561018	Capacitive sensor - KG600	IFM Electronic	\

Aspirator filters



Please check the kind of aspirator installed




Aspirator filters

<i>Picture</i>	<i>Code</i>	<i>Description</i>	<i>Supplier</i>	<i>Recommended pieces</i>
	5000008	Metallic prefilter	Dietronic	\
	5000009	Fiberglass pocket filter	Dietronic	1
	5000012	High efficiency HEPA filter	Dietronic	1
	5000018	Washable black panel filter	Dietronic	\
	5000070	Gaskets kit for aspirator	Dietronic	\



Please check the kind of aspirator installed





Aspirator filters

<i>Picture</i>	<i>Code</i>	<i>Description</i>	<i>Supplier</i>	<i>Recommended pieces</i>
	5000060	Cellulose cartridge filter	Dietronic	1
	5000061	Coalescence prefilter	Dietronic	1
	5000062	High efficiency HEPA filter	Dietronic	1





Please check the kind of aspirator installed

Main electric components

Picture	Code	Description and code	Supplier	Recommended pieces
	8593200	Power supply 24V – 85001	Murrelektronik	\
	8593201	Power supply 12V – 85016	Murrelektronik	\
	8562847	Programmed PLC - S71500	Siemens	\
	8562850	Programmed HMI - TP1900	Siemens	\

DT Wash

<i>Picture</i>	<i>Code</i>	<i>Description</i>	<i>Supplier</i>	<i>Recommended pieces</i>
	5002403 (20L)	DT Wash Cleaning product To clean the Hydraulic circuit and the tank	Dietronic	If the wash tank is present, we recommend having at least 40L of cleaning product always avaiable
	5002404 (200L)		Dietronic	